

PRODUCT INFORMATION

# MAXTECH

PAO050x19,5-Ø6x22,6 + ASBUS

EAN 4031582381221



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Diameter	1.97 in
Tread width	0.77 in
Axle hole diameter	0.24 in
Hub length	0.89 in

## CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.07 lb