PRODUCT INFORMATION

MAXTECH

PAO050x19,5-Ø6x22,6 + ASBUS

EAN 4031582381221

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Diameter	1.97 in
Tread width	0.77 in
Axle hole diameter	0.24 in
Hub length	0.89 in

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.07 lb

© Copyright 2026 TENTE International GmbH