

## ZETA

4688IFP125P63

EAN 4031582366068  
Order number 00837723



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ● |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Zeta                          |
| Housing type                | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 300 kg                        |
| Load capacity at 6 km/h     | 240 kg                        |
| Load capacity Static        | 600 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |
| Overall height              | 164 mm                        |
| Overall width               | 117 mm                        |
| Overall weight              | 1.798 kg                      |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Aluminium                             |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing                |
| Axle                  | Screwed with nut                      |
| Wheel color           | Grey / non- marking                   |
| Threadguards          | Without threadguard                   |
| Diameter              | 125 mm                                |
| Tread width           | 50 mm                                 |
| Body width            | 50 mm                                 |
| Hardness of tread (A) | 67 Shore A                            |

## HOUSING

|            |                         |
|------------|-------------------------|
| Material   | Steel sheet, very heavy |
| Fork shape | Broad, reinforced       |
| Colour     | Blue passivated         |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 137 mm            |
| Plate width                 | 117 mm            |
| Plate hole length (Minimum) | 75 mm             |
| Plate hole length (Maximum) | 80 mm             |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 105 mm            |
| Plate hole diameter         | 11 mm             |

# ZETA

4688IFP125P63

EAN 4031582366068  
Order number 00837723



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

