

PRODUCT INFORMATION

FOOTMASTER

FOOT MASTER GDR- 60-S-NYN

EAN 4031582413304



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

HOUSING

Housing Color	White
Offset	1.5 in
Swivel radius	2.48 in
Swivel interference	4.96 in
Dome diameter	2.76 in

WHEEL

Bearing	Roller bearing, damped
Wheel color	Black
Diameter	1.97 in
Tread width	0.98 in
Body width	0.98 in

PERFORMANCE

Roll Performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel caster
Load capacity at 1.8 mph	551.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	551.16 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	3.25 in
Overall width	2.76 in
Overall weight	1.54 lb

FOOTMASTER

FOOT MASTER GDR- 60-S-NYN

EAN 4031582413304

Order number 00062081
Product Drawings



BETTER MOBILITY. BETTER LIFE.

