

ALPHA

3477UFP125P30-13

EAN 4031582381504



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	6.1 in
Overall weight	2.9 lb

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Hardness of tread (A)	64 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.57 in
Swivel radius	4.76 in
Swivel interference	9.53 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA

3477UFP125P30-13

EAN 4031582381504



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

