

LINEA

5940UAP150P30-13

EAN 4031582408447



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●●●

Buka u pokretu ●●●●○

Ishrana ●●●●○

otpornost na rdju ●●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda	Linea
Tip	Okretanje Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	130 kg
Statički Nosivost	260 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	170 mm
Ukupna širina	89 mm
Ukupna težina	1,1 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
štitnici omotaca	Sa threadguard
Prečnik	150 mm
Širina omotac	22 mm
Teškoća gazećeg omotac (A)	92 Šor A

KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	precizini kuglicni lezaj
ofset	52 mm
okretni radijus	133 mm
Otpor okretanju	266 mm
Prečnik kupole	56 mm

PRILAGODAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

Deutscher
dizajner
ClubInterzum
nagradaIF nagrada za
Dizajn

TEHNIČKI CRTEŽI

