

PRODUCT INFORMATION

BASETECH

POR100x36-Ø12 white TFR

EAN 4031582390599



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Basetech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Electric Conductive	No
Stainless	No
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.14 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	36 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm
Hardness of tread (D)	69 Shore D

BASETECH

POR100x36-Ø12 white TFR

EAN 4031582390599



BETTER MOBILITY. BETTER LIFE.

Product Drawings

