

ALPHA STAINLESS

8477PIO080P62

EAN 4031582381641



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

| | |
|--------------------------------|---------------------------------|
| Naziv proizvoda | Alpha stainless |
| Tip | Okreni Tocak sa potpuna kocnica |
| Standard | EN12532 - transportna oprema |
| Nosivost na 4 km/h | 70 kg |
| nerdjajuci | ✓ |
| Statički Nosivost | 140 kg |
| Temperaturni opseg (Minimalno) | -20 °C |
| Opseg temperature (maksimalni) | 60 °C |
| Sveukupna visina | 108 mm |
| Ukupna težina | 0,875 kg |

TOCAK

| | |
|----------------------------|-------------------------------|
| Materijal za telo | polipropilen |
| materijal omotaca | Cvrsta guma, bez obeležavanja |
| Nošenje | klizni lezaj |
| osovina | Završena sa navrtkom |
| stitnici omotaca | Bez stražara |
| Prečnik | 80 mm |
| Širina omotac | 35 mm |
| Teškoća gazećeg omotac (A) | 80 Šešelj A |

KUCISTE

| | |
|-----------------|-------------------------|
| Materijal | nerdjajuci čelik, težak |
| oblik viljuska | siroko |
| okretni lezaj | Dve lopte |
| ofset | 44,5 mm |
| okretni radijus | 123 mm |
| Otpor okretanju | 246 mm |

PRILAGODAVANJE

| | |
|----------------------------------|-------------------|
| Tip uklapanja | Pravougaona ploča |
| Dužina ploče | 105 mm |
| Širina ploče | 80 mm |
| Dužina otvora ploče (Minimalno) | 77 mm |
| Dužina otvora ploče (maksimalna) | 80 mm |
| Širina otvora ploče (maksimalna) | 60 mm |
| Prečnik otvora ploče | 9 mm |

ALPHA STAINLESS

8477PIO080P62

EAN 4031582381641



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

B477U00080P62-neu

