

AGILA CARE US

2440UAP150R05-32

EAN 4031582387339



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila care US
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	7.6 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Hardness of tread (D)	40 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Precision ball bearing
Offset	1.97 in
Swivel radius	4.92 in
Swivel interference	9.84 in

FITTING

Fitting type	Solid stem, round
Bolt diameter	1.26 in
Bolt length	1.97 in