

# DURATECH HEAT

BOG080X35-Ø8 TFR

EAN 4031582392944



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Duratech heat
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.18 kg

## WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Diameter	80 mm
Tread width	35 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (D)	85 Shore D

# DURATECH HEAT

BOG080X35-Ø8 TFR

EAN 4031582392944



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

