

DURATECH

TOP 080x74-Ø20 HL80

EAN 4031582331028



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	700 kg
Nosivost na 6 km/h	560 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.45 kg

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	74 mm
dimenzija rupa osovina	20 mm
dužina glavnice	80 mm
Širina tela	74 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

