

SUPRATECH

PJO3X1.25-Ø0.5 HL40

EAN 4031582436013



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	76.2 mm
Tread width	31.75 mm
Axle hole diameter	12.1 mm
Hub length	40 mm
Hardness of tread (A)	77 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	Institute of Casters and Wheel Manufacturers
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg

SUPRATECH

PJO3X1.25-Ø0.5 HL40

EAN 4031582436013



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

