

# MAXTECH

PNP200X50-Ø8 HL53 GRIS

EAN 4031582439656



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	8 mm
Hub length	53 mm
Hardness of tread (A)	70 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.065 kg

# MAXTECH

PNP200X50-Ø8 HL53 GRIS

EAN 4031582439656



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

