

STORA

2370DIK075P30-10,3

EAN 4031582300291
Order number 00004832



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	55 kg
Load capacity Static	110 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	100 mm
Overall width	50 mm
Overall weight	0.415 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Body width	25 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	30 mm
Swivel radius	67.5 mm
Swivel interference	135 mm
Dome diameter	43.5 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10.3 mm

STORA

2370DIK075P30-10,3

EAN 4031582300291
Order number 00004832



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

