

PRODUCT INFORMATION

DURATECH

TOP082x88-Ø20 HL90

EAN 4031582322613



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	3.23 in
Tread width	3.46 in
Axle hole diameter	0.79 in
Hub length	3.54 in
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Load capacity at 1.8 mph	1984.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	3968.32 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	1.21 lb

DURATECH

TOP082x88-Ø20 HL90

EAN 4031582322613

Order number 00804433
Product Drawings



BETTER MOBILITY. BETTER LIFE.

