

PRODUCT INFORMATION

NOVATECH

FTP 200X80-Ø30 HL90

EAN 4031582319347
Order number 00828810



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	3.15 in
Axle hole diameter	1.18 in
Hub length	3.54 in
Body width	3.15 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Suitable for	linde

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	3703.76 lb
Load capacity at 3.7 mph	3086.47 lb
Load capacity Static	6172.94 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall weight	15.41 lb

NOVATECH

FTP 200X80-Ø30 HL90

EAN 4031582319347
Order number 00828810



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

