PRODUCT INFORMATION

# ALPHA

## 3478UFR100P62 tyre-5015

EAN 4031582306958

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●●○ |
| Movement Noise | ●●●●○ |
| Attrition | ●●●○○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Alpha |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 160 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 320 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 80 °C |
| Overall Height | 128 mm |
| Overall width | 85 mm |
| Overall weight | 0.49 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, heavy |
| Fork shape | Broad |
| Housing Color | Blue passivated |

### WHEEL

| | |
|---|---|
| Tread hardness | soft |
| Body material | Polyamide |
| Tread Material Mix | Elastic tire, non-marking, vulcanized |
| Bearing | Roller bearing |
| Axle | Screwed with nut |
| Wheel Color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 34 mm |
| Body width | 34 mm |
| Hardness of tread (A) | 63 Shore A |

### FITTING

| | |
|---|---|
| Fitting type | Small rectangular plate |
| Plate length | 103 mm |
| Plate width | 85 mm |
| Plate hole length (Minimum) | 77 mm |
| Plate hole length (Maximum) | 60 mm |
| Plate hole width (Minimum) | 77 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 9 mm |

© Copyright 2026 TENTE International GmbH


# ALPHA


3478UFR100P62 tyre-5015


EAN 4031582306958

Order number 00004019

**Product Drawings**




© Copyright 2026 TENTE International GmbH