

# LINEA LIGHT

5927UAI075S70-M10X15 KP LN EN12528 RAL7001

EAN 4031582414981



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Linea light                   |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12528 - Furniture Castors   |
| Load capacity at 3 km/h     | 60 kg                         |
| Load capacity Static        | 120 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall height              | 81 mm                         |
| Overall width               | 55 mm                         |
| Overall weight              | 0.21 kg                       |

## WHEEL

|                |                                |
|----------------|--------------------------------|
| Body material  | Polyamide                      |
| Tread material | Polyurethane, injected         |
| Bearing        | Plain bearing with spacer tube |
| Threadguards   | Without threadguard            |
| Diameter       | 75 mm                          |
| Tread width    | 15 mm                          |

## HOUSING

|                     |                    |
|---------------------|--------------------|
| Material fork       | Polyamide          |
| Fork shape          | Twin wheel housing |
| Swivel bearing      | Stem, swiveling    |
| Offset              | 23 mm              |
| Swivel radius       | 82 mm              |
| Swivel interference | 164 mm             |
| Thread diameter     | 0 mm               |

## FITTING

|              |                                      |
|--------------|--------------------------------------|
| Fitting type | Threaded stem with hexagon neck, top |
| Stem length  | 15 mm                                |



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award

## PRODUCT INFORMATION

# LINEA LIGHT

5927UAI075S70-M10X15 KP LN EN12528 RAL7001


EAN 4031582414981



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award