

# MAXTECH

PAO075x25-Ø8

EAN 4031582454291



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

|                             |         |
|-----------------------------|---------|
| Product Name                | Maxtech |
| Type                        | Wheel   |
| Load capacity at 3 km/h     | 60 kg   |
| Electric Conductive         | No      |
| Stainless                   | No      |
| Load capacity Static        | 120 kg  |
| Temperature range (Minimum) | -20 °C  |
| Temperature range (Maximum) | 60 °C   |
| Overall weight              | 0.08 kg |

## WHEEL

|                       |            |
|-----------------------|------------|
| Diameter              | 75 mm      |
| Tread width           | 25 mm      |
| Axle Hole Diameter    | 8.1 mm     |
| Hub Length            | 26.5 mm    |
| Hardness of tread (D) | 42 Shore D |