PRODUCT INFORMATION

MAXTECH

PAO075x25-Ø8

EAN 4031582454291

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Diameter	75 mm
Tread width	25 mm
Axle Hole Diameter	8.1 mm
Hub Length	26.5 mm
Hardness of tread (D)	42 Shore D

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.08 kg

© Copyright 2026 TENTE International GmbH