

ALPHA STAINLESS

8470IDG100P62 HT w/o-dustg traed-1023

EAN 4031582346701



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ● ○
Buka u pokretu	● ● ● ● ● ○
Ishrana	● ● ○ ○ ○ ○
otpornost na rdju	● ● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	80 kg
Električni provod	no
nerdjajuci	yes
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-30 °C
Opseg temperature (maksimalni)	250 °C
Sveukupna visina	128 mm
Ukupna širina	75 mm
Ukupna težina	1 kg

KUCISTE

Materijal kućišta	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
Boja	nerdjajuci čelik
ofset	41 mm
okretni radijus	91 mm
Otpor okretanju	182 mm
Prečnik kupole	75 mm

TOCAK

Tread hardness	mekan
Materijal za telo	Aluminijum
materijal omotaca	Vlažnost, otpornost na visoke temperature
Nošenje	gram sa suvim ležajem
osovina	Završena sa navrtkom
Boja Tocak	Metalni
stičnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	75 Šor A

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	105 mm
Širina ploče	85 mm
Dužina otvora ploče (Minimalno)	77 mm
Dužina otvora ploče (maksimalna)	60 mm
Širina otvora ploče (Minimalno)	77 mm
Širina otvora ploče (maksimalna)	80 mm
Prečnik otvora ploče	9 mm

ALPHA STAINLESS

8470IDG100P62 HT w/o-dustg traed-1023

EAN 4031582346701

Broj porudžbine 00035518

Product Drawings



BETTER MOBILITY. BETTER LIFE.

