

STEM

B10-10x20 / 10

EAN 4031582438048



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Axle	Riveted
------	---------

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	10 mm

PERFORMANCE

Corrosion Resistance	● ● ● ○ ○
----------------------	-----------

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Overall Height	4.5 mm
Overall weight	0.04 kg