PRODUCT INFORMATION

STEM

B10-10x20 / 10

EAN 4031582438048



Image may differ from the original product

PERFORMANCE

Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Stem
Type	Accessory
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Overall Height	4.5 mm
Overall weight	0.04 kg

WHEEL

Axle	Riveted

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	10 mm

© Copyright 2026 TENTE International GmbH