

# DURATECH SILENT

HUR125X36-Ø12 WHITE

EAN 4031582400694



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Damping, hybrid material
Tread material	Polyamide
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.73 in
Hardness of tread (D)	75 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech silent
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	1.22 lb

# DURATECH SILENT

HUR125X36-Ø12 WHITE

EAN 4031582400694



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

