

AGILA STAINLESS

7470PJH050P30-12,3

EAN 4031582351057



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Stainless	✓
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	69 mm
Overall width	43 mm
Overall weight	0.155 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Body width	19 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	24 mm
Swivel radius	49 mm
Swivel interference	98 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	12.3 mm
Hint	Castors can be mounted with standard screws of any length.

AGILA STAINLESS

7470PJH050P30-12,3

EAN 4031582351057



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

