

ALPHA STAINLESS

8477UFD125P30-11

EAN 4031582370195
Broj porudžbine 00038946



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●●

Ishrana ●●●○○

otpornost na rdju ●●●●●

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	150 kg
nerdjajuci	✓
Statički Nosivost	300 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	155 mm
Ukupna težina	1,174 kg

TOCAK

Materijal za telo	poliamid
	mekan
materijal omotaca	Elastična guma, neobeležena, vulkanizovana
Nošenje	kotrljajuci lezaj, nerdjajuci
osovina	Završena sa navrtkom
Prečnik	125 mm
Širina omotac	40 mm
Teškoća gazećeg omotac (A)	64 Šešelj A

KUCISTE

Materijal	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	40 mm
Otpor okretanju	242 mm

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	11 mm

ALPHA STAINLESS

8477UFD125P30-11

EAN 4031582370195
Broj porudžbine 00038946



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

