

# DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

|                       |                            |
|-----------------------|----------------------------|
| Body material         | Polyamide, super heavy     |
| Tread Material Mix    | Double flanged with tracks |
| Bearing               | Precision ball bearing     |
| Threadguards          | Without threadguard        |
| Diameter              | 50 mm                      |
| Tread width           | 26 mm                      |
| Axle Hole Diameter    | 15 mm                      |
| Hub Length            | 32 mm                      |
| Hardness of tread (D) | 75 Shore D                 |

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product Name                | Duratech plus                |
| Type                        | Wheel                        |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 240 kg                       |
| Load capacity at 6 km/h     | 200 kg                       |
| Electric Conductive         | No                           |
| Stainless                   | No                           |
| Load capacity Static        | 480 kg                       |
| Temperature range (Minimum) | -40 °C                       |
| Temperature range (Maximum) | 80 °C                        |

# DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370

Order number 00860912  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

