

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, super heavy
Tread Material Mix	Double flanged with tracks
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	50 mm
Tread width	26 mm
Axle Hole Diameter	15 mm
Hub Length	32 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech plus
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	240 kg
Load capacity at 6 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	480 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C

DURATECH PLUS

MMP050x26-Ø15

EAN 4031582399370

Order number 00860912
Product Drawings



BETTER MOBILITY. BETTER LIFE.

