

PRODUCT INFORMATION

MAXTECH

PNR389x85-Ø20 HL74 TFR

EAN 4031582400342



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

|                         |         |
|-------------------------|---------|
| Product Name            | Maxtech |
| Type                    | Wheel   |
| Load capacity at 3 km/h | 75 kg   |
| Electric Conductive     | No      |
| Stainless               | No      |
| Load capacity Static    | 150 kg  |
| Overall weight          | 1.95 kg |

WHEEL

|                    |                      |
|--------------------|----------------------|
| Body material      | Polypropylene        |
| Tread Material Mix | Polyurethane, foamed |
| Bearing            | Roller bearing       |
| Threadguards       | Without threadguard  |
| Diameter           | 389 mm               |
| Tread width        | 85 mm                |
| Axle Hole Diameter | 20 mm                |
| Hub Length         | 74 mm                |

