

COMPACTA

1430POI038P60-46x38

EAN 4031582336672



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	25 kg
Electric Conductive	No
Stainless	No
Load capacity Static	50 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	50.5 mm
Overall width	32 mm
Overall weight	0.07 kg

HOUSING

Housing Material	Steel sheet, light
Fork shape	Broad
Swivel Bearing	One ball race
Housing Color	Blue passivated
Offset	13 mm
Swivel radius	32 mm
Swivel interference	64 mm
Dome diameter	32 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	38 mm
Tread width	16 mm
Body width	16 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	46 mm
Plate width	38 mm
Plate hole length (Maximum)	28 mm
Plate hole width (Maximum)	36 mm
Plate hole diameter	5.3 mm

COMPACTA

1430POI038P60-46x38

EAN 4031582336672

Order number 00032083

Product Drawings



BETTER MOBILITY. BETTER LIFE.

