

# ALPHA STAINLESS

8478UOD160P63

EAN 4031582333084  
Order number 00038020



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ● |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Alpha stainless               |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 881.85 lb                     |
| Stainless                   | ✓                             |
| Load capacity Static        | 1763.7 lb                     |
| Temperature range (Minimum) | -13 °F                        |
| Temperature range (Maximum) | 176 °F                        |
| Overall height              | 7.87 in                       |
| Overall width               | 4.53 in                       |
| Overall weight              | 3.43 lb                       |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread material        | Identical with wheel body |
| Bearing               | Roller bearing, stainless |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Diameter              | 6.3 in                    |
| Tread width           | 1.57 in                   |
| Body width            | 1.57 in                   |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|            |                        |
|------------|------------------------|
| Material   | Stainless steel, heavy |
| Fork shape | Broad                  |
| Color      | Stainless steel        |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 5.39 in           |
| Plate width                 | 4.53 in           |
| Plate hole length (Minimum) | 2.95 in           |
| Plate hole length (Maximum) | 3.15 in           |
| Plate hole width (Minimum)  | 2.95 in           |
| Plate hole width (Maximum)  | 4.13 in           |
| Plate hole diameter         | 0.43 in           |

# ALPHA STAINLESS

8478UOD160P63

EAN 4031582333084  
Order number 00038020



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

