PRODUCT INFORMATION

ALPHA STAINLESS

8478BOG100P62

EAN 4031582347074

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●○○○
Attrition	●●●●●
Corrosion Resistance	●●●●●

CORE ATTRIBUTES

Product Name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Electric Conductive	No
Stainless	Yes
Load capacity Static	250 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	250 °C
Overall Height	128 mm
Overall width	85 mm
Overall weight	0.51 kg

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad
Housing Color	Stainless steel

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel Color	Black
Diameter	100 mm
Tread width	35 mm
Body width	35 mm
Hardness of tread (D)	90 Shore D

FITTING

Fitting type	Small rectangular plate
Plate length	100 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

© Copyright 2026 TENTE International GmbH


ALPHA STAINLESS


8478BOG100P62


EAN 4031582347074

Order number 00035519

Product Drawings







© Copyright 2026 TENTE International GmbH