

# NOVATECH

ITB125x50-Ø17 H7

EAN 4031582397888



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 500 kg                        |
| Load capacity at 6 km/h     | 400 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1000 kg                       |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 60 °C                         |
| Overall weight              | 0.8 kg                        |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Aluminium            |
| Tread Material Mix    | Polyurethane, casted |
| Bearing               | Bore with keyway     |
| Threadguards          | Without threadguard  |
| Diameter              | 125 mm               |
| Tread width           | 50 mm                |
| Axle Hole Diameter    | 17 mm                |
| Hub Length            | 54 mm                |
| Hardness of tread (D) | 42 Shore D           |

