

NOVATECH

FTP 140x60-Ø20 HL68 cv R190

EAN 4031582329421



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE


Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	840 kg
Nosivost na 6 km/h	700 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	2.76 kg

TOCAK

Tread profile	konveksan
Materijal za telo	Ливено Гвожђе
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	140 mm
Širina omotac	60 mm
dimenzija rupa osovina	20 mm
duzina glavine	68 mm
Širina tela	60 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D
Tip ležaja	6304
Pogodno za	bt




NOVATECH

FTP 140x60-020 H168 cv R190

EAN 4031582389421

Broj porudžbine 00831769



BETTER MOBILITY. BETTER LIFE.