

DURATECH

UOR125X43-Ø20 HL 58 TFR

EAN 4031582392975



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	43 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.476 kg

DURATECH

UOR125X43-Ø20 HL 58 TFR

EAN 4031582392975



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

