PRODUCT INFORMATION

AGILA

2478DIK075P60-67x60

EAN 4031582030082



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●●○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	121.25 lb
Electric conductive	no
Stainless	no
Load capacity Static	242.51 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.94 in
Overall width	1.69 in
Overall weight	0.69 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	1.69 in

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Rectangular plate
Plate length	2.64 in
Plate width	2.36 in
Plate hole length (Minimum)	1.57 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.57 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

© Copyright 2026 TENTE International GmbH


AGILA


2478DIK075P60-67x60

EAN 4031582030082

Order number 00004890

Product Drawings





© Copyright 2026 TENTE International GmbH