

ALPHA

3478UFP125P62

EAN 4031582327649
Order number 00026480



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall height	6.1 in
Overall width	3.35 in
Overall weight	1.83 lb

WHEEL

Body material	Polyamide
	soft
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.57 in
Body width	1.57 in
Hardness of tread (A)	63 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Color	Blue passivated

FITTING

Fitting type	Rectangular plate
Plate length	4.06 in
Plate width	3.35 in
Plate hole length (Minimum)	3.03 in
Plate hole length (Maximum)	2.36 in
Plate hole width (Minimum)	3.03 in
Plate hole width (Maximum)	3.15 in
Plate hole diameter	0.35 in

ALPHA

3478UFP125P62

EAN 4031582327649
Order number 00026480



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

Technical drawing of a wheel assembly (part number 3478 125P62) showing front, side, and top views with dimensions and a 3D perspective view.

Dimensions:

- Front view: $\varnothing 125 \pm 0,2$, 85 ± 0,2, 77 ± 0,2, 59 ± 0,02, 103 ± 0,1, 57 ± 0,02, 86 ± 0,1
- Side view: 85 ± 0,2, 46 ± 0,1

3D perspective view: 12

Shuttermark 100 10216 beachten
Weitergabe ohne Genehmigung dieser Zeichnung, Vervielfältigung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Urheberrechts- oder Geschäftsgeheimnisverletzung vorbehalten.

Achtung! Zeichnungsänderungen nur nach Freigabe!
attention! amendment of drawing only after release!

Notice the protective note 100 10216
The reproduction, distribution and utilization of the drawing as well as the communication of this content to others without explicit authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Allgemein		Oberfläche		Maßstab: 1:1, 1:2		mit Holzfeder einbaufähig	
Material		Beschreibung		Verkaufst.		<input type="checkbox"/> Flansche <input type="checkbox"/> ohne Flansche <input type="checkbox"/> ohne Flansche	
3478	125P62			3478	125P62		
TENTE				TR11457		B01	
City	Address	Street	Postcode	City	St. Nr.	St. Nr.	St. Nr.