

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	720 kg
Nosivost na 6 km/h	600 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.38 kg

DURATECH


TOO 100x50-Ø20 HL60

EAN 4031582322491

Broj porudžbine 00804809
Product Drawings



BETTER MOBILITY. BETTER LIFE.




DURATECH

TOO 100x50-Ø20 HL50

EAN 4031582322494

Broj porudžbine 00804809



BETTER MOBILITY. BETTER LIFE.