

# AGILA

2470PIO075R07-Ø19-21,5

EAN 4031582371277



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 60 kg                     |
| Load capacity Static        | 120 kg                    |
| Temperature range (Minimum) | -10 °C                    |
| Temperature range (Maximum) | 40 °C                     |
| Overall height              | 103 mm                    |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 75 mm                     |
| Tread width           | 25 mm                     |
| Hardness of tread (A) | 87 Shore A                |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 24 mm               |
| Swivel radius       | 61.5 mm             |
| Swivel interference | 123 mm              |

## FITTING

|                            |                                                            |
|----------------------------|------------------------------------------------------------|
| Fitting type               | Synthetic expander, round                                  |
| Expander fitting (Minimum) | 19 mm                                                      |
| Expander fitting (Maximum) | 21.5 mm                                                    |
| Hint                       | Please indicate required tube innerdiameter when ordering. |

# AGILA

2470PIO075R07-Ø19-21,5

EAN 4031582371277



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

