

PRODUCT INFORMATION

MAXTECH

DNP200x50-Ø20x50

EAN 4031582380996



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|--------------------|------------------------|
| Body material | Sheet Steel |
| Tread material | Polyurethane, foamed |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 7.87 in |
| Tread width | 1.97 in |
| Axle hole diameter | 0.79 in |
| Hub length | 1.97 in |

CORE ATTRIBUTES

| | |
|--------------------------|-----------|
| Product name | Maxtech |
| Type | Wheel |
| Load capacity at 1.8 mph | 165.35 lb |
| Electric conductive | Yes |
| Stainless | no |
| Load capacity Static | 330.69 lb |
| Overall weight | 1.9 lb |

MAXTECH

DNP200x50-Ø20x50

EAN 4031582380996



BETTER MOBILITY. BETTER LIFE.

Product Drawings

