

R47-21,5-24 INOX

EAN 4031582428292



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall weight	0.126 kg

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	21.5 mm
Expander fitting (Maximum)	24 mm
Hint	Please indicate required tube innerdiameter when ordering.