

# ELASTECH HEAT

IDG100x35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Tread hardness	soft
Body material	Aluminium
Tread Material Mix	Damping, heat resistant
Bearing	Dry bearing bush
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle Hole Diameter	8 mm
Hub Length	45 mm
Hardness of tread (A)	75 Shore A

## PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product Name	Elastech heat
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Electric Conductive	Yes
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	250 °C
Overall weight	0.35 kg

# ELASTECH HEAT

IDG100x35-Ø8 (DSG)

EAN 4031582382594



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

