PRODUCT INFORMATION

# INTEGRAL

## 2046UAX200R26-28S30 4xM8

EAN 4031582453515



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Integral |
| Type | Swivel castor with central, total lock |
| Standard | similar EN12531- Hospital Bed Castors |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 300 kg |
| Temperature range (Minimum) | -30 °C |
| Temperature range (Maximum) | 80 °C |
| Overall Height | 229 mm |
| Overall weight | 1.68 kg |
| Certification | Tested and monitored by TÜV Süd |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Closed |
| Swivel Bearing | Precision ball bearing |
| Offset | 60 mm |
| Swivel radius | 160 mm |
| Swivel interference | 320 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing, sealed |
| Threadguards | Integrated threadguard |
| Diameter | 200 mm |
| Tread width | 35 mm |
| Hardness of tread (D) | 59 Shore D |

### FITTING

| | |
|---|---|
| Brake cam | hex cam |
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm |
| Bolt length | 96 mm |
| Hint | Washable beds must be sealed in the fitting area by the hospital bed manufacturer. |

IF Design Award

Red Dot Design Award

© Copyright 2026 TENTE International GmbH


# INTEGRAL

2046UAX200R26-28S30 4xM8

EAN 4031582453515

BETTER MOBILITY. BETTER LIFE.

## Product Drawings




IF Design Award

Red Dot Design Award

© Copyright 2026 TENTE International GmbH