

ALPHA STAINLESS

8470UAO200P63 BURDEOS

EAN 4031582441826



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Housing type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 350 kg |
| Load capacity Static | 700 kg |
| Temperature range (Minimum) | -40 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 240 mm |
| Overall weight | 2 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material fork | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Offset | 55 mm |
| Swivel radius | 155 mm |
| Swivel interference | 310 mm |
| Stainless | ✓ |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 105 mm |
| Plate width | 80 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 80 mm |
| Plate hole diameter | 11 mm |

ALPHA STAINLESS

8470UAO200P63 BURDEOS

EAN 4031582441826



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

B470U00125P62-neu

