

GALEA STAINLESS

5080PJM100P60-90X70

EAN 4031582308693



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Galea stainless
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Stainless	✓
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	5.43 in
Overall weight	0.94 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing, stainless
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.18 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races, reinforced or stainless
Offset	1.57 in
Swivel radius	3.54 in
Swivel interference	7.09 in

FITTING

Fitting type	Rectangular plate
Plate length	3.54 in
Plate width	2.76 in
Plate hole length (Minimum)	2.36 in
Plate hole length (Maximum)	2.76 in
Plate hole width (Minimum)	1.97 in
Plate hole width (Maximum)	2.17 in
Plate hole diameter	0.31 in

GALEA STAINLESS

5080PJM100P60-90X70

EAN 4031582308693



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

