

ALPHA STAINLESS

8477IDC100P30-13 TFR

EAN 4031582480443



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	176.37 lb
Stainless	✓
Load capacity Static	352.74 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	482 °F
Overall height	5.04 in

WHEEL

Body material	Aluminum
	soft
Tread material	Damping, heat resistant
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Hardness of tread (A)	75 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	4.76 in
Swivel interference	9.53 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in