

# PLATE

P41-38x38 / 10 drilled plate

EAN 4031582411928



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## FITTING

Fitting type	Square plate
Plate length	38 mm
Plate width	38 mm
Plate hole length (Maximum)	27 mm
Plate hole width (Maximum)	27 mm
Plate hole diameter	5 mm

## PERFORMANCE

Corrosion Resistance ●●●○○

## CORE ATTRIBUTES

Product Name	Plate
Type	Accessory
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Overall Height	10 mm
Overall weight	0.05 kg