

PRODUCT INFORMATION

PURETECH

FVP 200X75-Ø20 HL90

EAN 4031582319514
Order number 00801897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Casting
	soft
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	7.87 in
Tread width	2.95 in
Axle hole diameter	0.79 in
Hub length	3.54 in
Body width	2.95 in
Hardness of tread (A)	67 Shore A

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1102.31 lb
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	13.03 lb

PURETECH

FVP 200X75-Ø20 HL90

EAN 4031582319514
Order number 00801897



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

