

PURETECH

PIR100X35-Ø8 HL44,4

EAN 4031582453164



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Solid rubber, non-marking |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.38 in |
| Axle hole diameter | 0.31 in |
| Hub length | 1.75 in |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Puretech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 165.35 lb |
| Load capacity Static | 330.69 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 0.62 lb |

PURETECH

PIR100X35-Ø8 HL44,4

EAN 4031582453164



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

