PRODUCT INFORMATION

# MAXTECH

## UAP 200x50-Ø25 HL60 natural/3004

EAN 4031582323061



Image may differ from the original product

### WHEEL

| | |
|---|---|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel Color | Natural white |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 50 mm |
| Axle Hole Diameter | 25 mm |
| Hub Length | 60 mm |
| Body width | 50 mm |
| Hardness of tread (A) | 96 Shore A |
| Hardness of tread (D) | 48 Shore D |

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ●●●○○ |
| Movement Noise | ●●●○○ |
| Attrition | ●●●●○ |
| Corrosion Resistance | ●●●○○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Maxtech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 500 kg |
| Load capacity at 6 km/h | 400 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 1000 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall weight | 1.17 kg |

© Copyright 2026 TENTE International GmbH


# MAXTECH

## UAP 200x50-Ø25 HL60 natural/3004

EAN 4031582323061

Order number 00034873

**Product Drawings**




© Copyright 2026 TENTE International GmbH